

WIKA'S TEN ETM-MRO MODELS FOR 5-DAY DELIVERY

RTD - RESISTANCE TEMPERATURE DETECTOR MODELS:

TR10-2: Industrial RTD Assembly, Head-Nipple-Union-Nipple Design, Various element lengths available, Direct mount into Thermowell, Transmitters available

TR15-2: Remote Mounted Industrial RTD Assembly, Various cable and element lengths available, Inserted into Process or Thermowell, Transmitters available

TR40: Industrial RTD Sensor, Metal sheathed elements with various lengths, With or without bushings, With insulated lead wires

TR45: Hollow Cut-To-Length RTD Sensor, Temporary replacement for failed MGO packed sensor, Minimizes downtime

TC - THERMOCOUPLE MODELS:

TC10-2: Industrial TC Assembly, Head-Nipple-Union-Nipple Design, Various element lengths available, Direct mount into Thermowell, Transmitters available

TC15-2: Remote Mounted Industrial TC Assembly, Various cable and element lengths available, Inserted into Process or Thermowell, Transmitters available

TC40: Industrial TC Sensor, Metal sheathed elements with various lengths, With or without bushings, With insulated lead wires

TC45: Hollow Cut-To-Length TC Sensor, Temporary replacement for failed MGO packed sensor, Minimizes downtime

TW - THERMOWELL MODELS:

TW10: Flanged Thermowell, Solid Machined, 1-2" 150# RF or 300# RF Design, 316 SS or 304 SS Material, Various lengths available, Tapered or Stepped Style

TW15: Threaded Thermowell, Solid Machined, 316 SS or 304 SS Material, Various Lengths available, Tapered or Stepped Style

Note: For faster deliveries, contact your local WIKA Sales Channel listed below.